


[See all 6 Products in Family](#)

TECHSPEC® 4.0mm Diameter x 4.0mm Length, N-LASFN9 Half-Drum Lens



Stock #46-531 CLEARANCE **1 In Stock**

€24²⁵

ADD TO CART

Volume Pricing	
Qty 1+	€24,25 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Half-Drum Lens Type:

Physical & Mechanical Properties

4.00 Diameter (mm):

4.00 Length (mm):

±30 Length Tolerance (µm):

Radius R (mm):
2.50

Radius Tolerance (µm):
+0/-1.5

Diameter Tolerance (µm):
+0/-50

Optical Properties

Substrate:
N-LASF9

Coating:
Uncoated

Wavelength Range (nm):
380 - 2500

Index of Refraction (n_d):
1.850

Surface Quality:
40-20

Regulatory Compliance

Certificate of Conformance:
[View](#)

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Easier to Mount and Handle Than Standard Ball Lenses

Drum lenses are glass spheres, ground down axially to provide a mounting surface. The ground circumference D simplifies handling issues typically associated with ball lenses. Ideal for optical transmission in fiber communications. Type B Drum lenses have a polished plano-surface for direct fiber contact and perform as elongated PCX lenses.

Technical Information

D	Radius R	Length	Length L2	Stock No.
Type A Drum Lenses				
2mm	1.25mm	2.5mm	1.5mm	#45-548
				#45-739
				#45-836
				#45-663
				#45-743
2.4mm	1.5mm	3mm	1.8mm	#45-549
				#45-837
				#45-664
				#45-744
3.2mm	2mm	4mm	2.4mm	#45-550
				#45-741
				#45-838
				#45-665
4mm	2.5mm	5mm	3mm	#45-745
				#45-551
				#45-839
				#45-742
#45-666				
Type B Half-Drum Lenses				
2mm	1.25mm	2mm	1.5mm	#46-524
				#46-528

2.4mm	1.5mm	2.4mm	1.8mm	#46-525
				#46-529
3.2mm	2mm	3.2mm	2.4mm	#46-526
				#46-530
4mm	2.5mm	4mm	3mm	#46-527
				#46-531

