

[See all 9 Products in Family](#)

35mm Focal Length Lens, 1" Sensor Format



35mm Focal Length Lens, 1" Sensor Format, #63-247

Stock **#63-247** **5 In Stock**

[Similar Products](#)

⊖ 1 ⊕ €761⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | €761,00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Product Family:
1" Format Fixed Focal Length Lenses

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:
Variable

| | |
|-------|-------------------------------|
| 43.00 | Length (mm): |
| 42.0 | Maximum Diameter (mm): |
| 42 | Outer Diameter (mm): |
| 130 | Weight (g): |

Optical Properties

| | |
|--------------|---|
| 20.9° | Horizontal Field of View, 1" Sensor: |
| 16.00 | Maximum Image Circle (mm): |
| <-0.5 | TV Distortion (%): |
| 35.00 | Focal Length FL (mm): |
| 300 - ∞ | Working Distance (mm): |
| f/1.4 - f/16 | Aperture (f/#): |
| < -0.05% | Maximum Distortion (%): |
| VIS | Lens Wavelength Range: |

Sensor

| | |
|------|-------------------------------|
| 1" | Maximum Sensor Format: |
| 5.00 | Pixel Size (µm): |

Threading & Mounting

| | |
|--------------|-----------------------|
| M35.5 x 0.50 | Filter Thread: |
| C-Mount | Mount: |

Regulatory Compliance

| | |
|----------------------------------|------------------------------------|
| Exempt | RoHS 2015: |
| View | Certificate of Conformance: |
| Contains SVHC(s) | REACH 241: |

Product Details

- Up to 1", C-Mount Lens
- "Fast" Lenses for Increased Throughput
- 4.7mm to 75mm Focal Length

1" Format Fixed Focal Length Lenses provide high throughput and high resolution across the entire camera sensor, allowing for excellent imaging even in less-than-ideal lighting conditions. Offered in 9 focal lengths from 4.7mm to 75mm, this complete family covers many of the applications in the market today. Engineered to minimize distortion, these lenses provide a perfect image for a human operator or an automated system. 1" Format Fixed Focal Length Lenses also feature a standard C-Mount lens mount for easy integration with the most common machine vision [cameras](#) we offer. All lenses feature front filter threading to attach to your choice of [optical filter](#).