

5mm FL, f/5.6, Low Distortion M12 Lens



5mm FL, Low Distortion M12 Lens

Stock **#75-216** NEW [CONTACT US](#)

-

1

+

€241⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€241,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

M12 Imaging Lens

Imaging Lens Type:

Physical & Mechanical Properties

Fixed

Iris Option:

29.90

Length (mm):

Maximum Diameter (mm):


21.5	
21.5	Outer Diameter (mm):
12	Weight (g):
29.90	Maximum Length (mm):
Optical Properties	
Horizontal Field of View @ Max Sensor Format: 59.8°	
Field of View at Max Sensor Format: Horizontal: 59.8° Vertical: 46.2° Diagonal: 71.8°	
5.00	Focal Length FL (mm):
100 - ∞	Working Distance (mm):
f/5.6	Aperture (f/#):
-0.51	Maximum Distortion (%):
-25.4	Exit Pupil Position (mm):
VS	Lens Wavelength Range:
Sensor	
1/1.8"	Optimized Sensor Format:
1/1.8"	Maximum Sensor Format:
Threading & Mounting	
S-Mount (M12 x0.5)	Mount:
Environmental & Durability Factors	
-20 to +60	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details


- Distortion as low as -0.02%
- Up to 1/1.8", S-Mount Options
- 1.7mm - 5mm Focal Lengths

Ultra Low Distortion Wide Angle Lenses are designed to achieve less than -0.02% distortion over a 76.9° field of view, less than -0.32% distortion over a 109.1° field of view, or less than -0.51% distortion over a 59.8° field of view. The ultra-low distortion values of these lenses ensure imaging with straight lines and natural object shapes, helping to reduce post-processing requirements. These lenses offer high transmission from the VS to NIR and are available in focal lengths of 1.70, 3.00, and 5.00mm. Ultra Low Distortion Wide Angle Lenses' low focal lengths allow for capturing more of the scene in a single frame. These lenses are ideal for surveillance, security, robotics, drive assistance systems, and [factory automation applications](#).


Technical Information




5mm FL, f/5.6, Low Distortion M12 Lens, Distribution Plot



5mm FL, f/5.6, Low Distortion M12 Lens, MTF Plot



5mm FL, f/5.6, Low Distortion M12 Lens, Relative Illumination Plot



5mm FL, f/5.6, Low Distortion M12 Lens, Transmission Plot