

TECHSPEC[®] 15.0mm Diameter, C-Mount Helicoid Barrel



C-Mount Helicoid Movement Barrel, #11-131



Stock **#54-392** 20+ In Stock

-

1

+

€451^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€451,00 each
Qty 5-9	€398,60 each
Qty 10-25	€367,10 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Helicoid Barrel

Type:

Circular	Type of Optics:
Optic MOUNT (Linear Adjustment)	Function:
Physical & Mechanical Properties	
7.5	Travel (mm):
31.8	Extension Length (mm):
34.8	Total Length (mm):
30.0	Outer Diameter (mm):
13.5	Clear Aperture CA (mm):
13.75	Max. Thickness of Compatible Optics (mm):
2.0	Min. Thickness of Compatible Optics (mm):
Threading & Mounting	
15.0	Diameter of Compatible Optics (mm):
0.75 x32 TPI	Barrel Thread:
C-Mount	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

Product Details

- Compatible With 12.5mm, 15mm, and 25mm Diameter Optics
 - Male and Female C-Mount Threads
 - Provides Linear Travel Without Rotating Optical Components
- TECHSPEC® C-Mount Helicoid Barrels provide smooth helical movement with precision controlled focusability to a system, without rotating the mounted optical component. These barrels are ideal for easy integration into any C-Mount system, such as [Tube Systems](#) or Imaging Systems and are available for mounting 12.5mm, 15mm, and 25mm diameter optics. These barrels feature a small maximum linear travel of 16mm for the 12.5 and 25mm versions, and 7.5mm maximum travel for the 15mm mounted optic version.
- Note:** TECHSPEC 15.0mm Diameter, C-Mount Helicoid Barrel ([#54-392](#)) requires two optional accessory retainer rings ([#54-395](#)) for fixing the optical element. There are also available adapters for mounting 15mm achromatic relay lenses and high-performance relay lenses ([#54-394](#) and [#54-721](#), respectively). To mount multiple optics into the TECHSPEC 12.5mm Diameter, C-Mount Helicoid Barrel ([#57-649](#)), please use the accessory retainer ring [#59-240](#).
- Note:** Accessories are required for operation and sold separately. The adapters thread into the helicoid's inner barrel. One retainer ring is required to position the lens adapters, or two can be used to maintain a fixed position. Two 1.5mm wide slots are provided on each accessory to accommodate a spanner wrench. Two retainer rings can also be used to hold a TECHSPEC® lens with a 15mm diameter in place.

Technical Information

