

[See all 23 Products in Family](#)

InfiniTube FM-200 with InLine Attachment for +10X Objectives

See More by [Infinity Photo-Optical Company](#)



InfiniTube FM-200 (1X), #58-310



Stock **#58-311** **3 In Stock**

⊖ 1 ⊕ €1.675⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€1.675,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Fixed Magnification Lens **Type:**
In-Line Illumination **Type of Illumination:**

Optical Properties

Primary Magnification PMAG:

Objective Required

Sensor

Maximum Sensor Format:

2/3"

Threading & Mounting

Mount:

C-Mount

Regulatory Compliance

RoHS 2015:

Compliant

Reach 224:

Compliant

Certificate of Conformance:

[View](#)


Product Details

- Direct to Video C-Mount for 2/3" and Smaller Sensor Cameras
- Internal Focusing

InfiniTube™ FMSystems are used to mount infinite-conjugate objectives to C-mount cameras, yielding magnifications not possible with ordinary video lenses, such as 50X magnification. The InfiniTube™ system can be configured in a variety of fashions. It can be utilized alone (InfiniTube™ #58-310 or #58-309) for applications where illumination is provided from another source such as a backlight or directional illumination. The InfiniTube™ FMSystems can also be configured for in-line illumination with attachments. The first in-line attachment (#58-313) has been designed for high performance with objectives having a magnification of 10X or below and is not suggested for use with higher magnification objectives. The second in-line attachment (#58-312) has been designed to work with increased efficiency when used with magnifications of 10X or higher, but can be utilized with all magnifications. All in-line attachments accept our [Fiber Optic Light Guides](#) with a 0.312" tip diameter.

Note: [Standard system](#) for 2/3" sensors still available.

Technical Information



Note:
The PL-Series Objectives are specifically designed to be used directly (no adapters required) with the InfiniTube™ FM-Series Main Bodies.
All PL-Series Objectives are amplified by 2X (InfiniTube FM-100) or 4X (InfiniTube™ FM-200) their engraved initial power ratings.
A DL 2X Tube can be used atop InfiniTube™ FM-Series Main Bodies to further amplify magnification by a 2X factor.

System Includes	Stock No.
InfiniTube In-Line Assembly Unit	#58-311
Hitachi KP-D20B Camera	#55-837
15.1" Diagonal LCD Monitor (US version only)	#56-522
Y-C Cable (6 ft.)	#39-255
Mitutoyo/Achrovid™ Objective Adapter	#58-316
M-150 Fiber Optic Illuminator	#55-718
Fiber Optic Light Guide (48" L)	#39-367
Fiber Optic Adapter	#38-944
Standard Boom Stand	#54-120
Rack & Pinion Mounting Plate	#54-123
C-Clamp with 1/4-20 Mounting Hole	#57-788