

Lumenera INFINITY 8-9C Microscopy Color Camera

See More by [Teledyne Lumenera](#)



Stock #25-355 1 In Stock

-

1

+

€4.900⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€4.900,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

Color

Spectrum:

General

Color Microscopy Camera	Type:
i8-LC00-09M	Model Number:
Teledyne Lumenera	Manufacturer:
INFINITY	Camera Series:

Physical & Mechanical Properties

41.5 x 45 x 45 (includes lens mount)	Dimensions (mm):
108	Weight (g):
Full	Housing:

Sensor

128MB	Image Buffer:
1"	Sensor Format:
8.90	Resolution (Megapixels):
31.00	Frame Rate (fps):
4,112 x 2,176	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
14.19 x 7.51	Sensing Area, H x V (mm):
Sony IMX267	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/12 bit	Pixel Depth:
73.3	Dynamic Range (dB):

Electrical

2.3 - 3.6	Power Consumption (W):
-----------	------------------------

Hardware & Interface Connectivity

USB 3.1	Interface:
Power over USB	Power Supply:
Not Specified	GPIOs:
Hardware Trigger (GPIO)	Synchronization:
Side Panel	Interface Port Orientation:
9-pin Hirose (JST)	GPIO Connector Type:

Threading & Mounting

C-Mount	Mount:
M3x0.5 (Integrated into Housing)	Mounting Threads:

Environmental & Durability Factors

0 to +50	Operating Temperature (°C):
-30 to +70	Storage Temperature (°C):

Regulatory Compliance

	Certificate of Conformance:
--	-----------------------------

PRODUCT DETAILS

- Exceptional Low Light Sensitivity
- Ideal for Life Sciences, Clinical, and Industrial Applications
- Affordable Price Point with Included Microscopy Software



Teledyne Lumenera INFINITY8 Microscopy Cameras offer an affordable solution for low light imaging in a compact form factor. Featuring low noise and large pixels, these cameras are ideal for a wide range of lighting conditions including the low light levels common in fluorescence imaging. Available with 1/1.8", 2/3", and 1" sensor sizes and megapixel range of 2 – 20 MP, each camera is compatible with Windows and Mac operating systems. Teledyne Lumenera INFINITY8 Microscopy Cameras include an INFINITY ANALYZE 7 software license, for camera operation and immediate analysis of the imaging results, and 3m Micro-B to Type-A USB cable.
