

## LUMIMAX® LED Ring 850nm Light OD 150mm



LUMIMAX® Configurable Ring Lights

Stock **#90-906** NEW **1 In Stock**

⊖ 1 ⊕ €1.195<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€1.195,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

101.0087.01.08.20 **Model Number:**

80000 **LED Lifetime (hours):**

LED Illuminator **Type of Illumination:**

**Note:**  
Extension cables and [#66-855](#) (Japan: [#89-513](#))  
required for operation under 'Accessories'.  
Optional intensity controller [#90-883](#) is available

LUMIMAX®	<b>Manufacturer:</b>
Ring	<b>Geometry:</b>
Constant	<b>Illumination Mode:</b>

## Physical & Mechanical Properties

150	<b>Outer Diameter (mm):</b>
78 ID x 135 OD	<b>Dimensions (mm):</b>
530	<b>Weight (g):</b>

## Optical Properties

NIR	<b>Color:</b>
850	<b>Wavelength (nm):</b>

## Hardware & Interface Connectivity

M16 12-pin plug (male)	<b>Connector:</b>
19 - 30 VDC	<b>Input Voltage (V):</b>

## Environmental & Durability Factors

5 to 45 non-condensing	<b>Operating Temperature (°C):</b>
IP64	<b>Environmental Rating:</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

## Product Details

- Wide Range of Available Accessories for Configurable Illumination Solutions
- Available in White, Blue (470nm), Green (528nm), Red (625nm), NIR (850nm) Wavelengths
- Ideal for Flat, Matte, and Reflective Object Surfaces

LUMIMAX® Ring Lights deliver bright, uniform illumination for demanding machine vision applications requiring optimal lighting geometry and color flexibility. Available in White, Blue (470nm), Green (528nm), Red (625nm), and NIR (850nm), these 150mm outer diameter LED ring lights provide consistent, shadow-free illumination for high-contrast imaging. A wide range of accessory kits is available to match specific inspection tasks. The lens array kit (#90-916) includes 12°, 31°, and 49° lens arrays for user-configurable field of view and working distance requirements. The dome extension kit (#90-913) converts the ring light to a highly diffuse homogeneous illuminator for inspection of reflective, curved, or uneven surfaces. The window kit (#90-915) includes a window, diffuser, and polarizer for control of transmission and glare. An optional LUMIMAX Control Box (#90-883) simplifies power management and brightness adjustment, ensuring stable and consistent illumination performance. LUMIMAX® Ring Lights are ideal for applications such as electronics inspection, surface defect detection, and automated optical inspection, and offer versatile and reliable illumination solutions.