

[All Products](#) / [Lab and Production](#)
/ [Preloaded Norland Optical Adhesive](#)

[See all 78 Products in Family](#)

Preloaded Norland Optical Adhesive (10cc)

See More by [Norland](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit



10cc Dispensing Barrel for NOA (NOA 60 shown as an example)

Stock #17-368 **2 In Stock**

1

€39^{,50}

ADD TO CART

Volume Pricing	
Qty 1-4	€39,50 each
Qty 5-11	€35,60 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads	
	Safety Data Sheet
	Spec Sheets:pdf
	EO Spec Sheet
Download All	

General

Size (oz): 0.34	Norland Number: 76
Shelf Life: 4 months	Type: Barrel
Typical Applications: Bonding acrylic, polycarbonate, and other plastics to glass	Note: Contains 10g of adhesive

Optical Properties

Index of Refraction (n_d): 1.51	Absorption Range (nm): 315 - 450
--	---

Material Properties

Glass Bonding: Excellent	Metal Bonding: Good
Plastic Bonding: Excellent	Viscosity (cps): 3500 - 5500
Bonding Type: Glass to Plastic	Energy for Full Cure (J/cm²): 5

Environmental & Durability Factors

Durability: Soft & Resilient

Regulatory Compliance

RoHS 2015: Compliant	Certificate of Conformance: View
------------------------------------	---

Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Norland Optical Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tip
- **Applicator and Bulk Bottles** of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a **dispensing unit** and **dispensing tips** for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Technical Information

Title	Description
Applying Adhesive	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
Chemical Resistance of NOA	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
Preventing Lens Separations with NOA	Covers best practices to avoid adhesive failures when bonding optical elements.
Separating Lenses Bonded with NOA	Covers how to unbond optical elements bonded with Norland Optical Adhesives.


Related Products



Dispenser Barrels and Accessories



Dispensing Guns and Hand Plungers



Handheld UV Curing Lamps

Frequently Purchased Together



#36-427 - Norland Optical Adhesive NOA 68, 1 oz. Application Bottle
€41,50



#45-935 - 6.0mm Diameter, N-BK7 Half-Ball Lens
€57,50



#45-936 - 8.0mm Diameter, N-BK7 Half-Ball Lens
€63,00



#37-322 - Norland Optical Adhesive NOA 61, 1 oz. Application Bottle
€41,50

Qty 

Qty 

Qty 

Qty 

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: