

[See all 20 Products in Family](#)

## Z-Axis Manual Focus Unit for Mitutoyo Video Microscope Unit

See More by [Mitutoyo](#)



Stock #71-011 [CONTACT US](#)

⊖ 1 ⊕ €4.300<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €4.300,00 each                |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### Physical & Mechanical Properties

50 Travel (mm):

2900 Weight (g):

17.4 Load Capacity (kg):

### Regulatory Compliance





| Mitutoyo Video Microscope Unit (VMU) and Mitutoyo Turret |                                |                         |                                   |   |                                       |            |
|--|--------------------------------|-------------------------|-----------------------------------|---|---------------------------------------|------------|
| Wavelength Range:  | VIS-NIR                        |                         | NUV-VIS-NIR Nd:YAG 355/532/1064nm | VIS-NIR-SWIR Widefield Hi-Res               | VIS Widefield BD                      |            |
| Type:  | Brightfield                    |                         | Brightfield                       | Brightfield                                 | Brightfield/Darkfield                 |            |
| Orientation:   | Vertical                       | Horizontal              | Vertical                          | Vertical                                    | Vertical                              | Horizontal |
| Model:   | 378-505                        | 378-506                 | 378-507                           | 378-519                                     | 378-517                               | 378-518    |
| Tube Lens Magnification:                                 | 1X                             |                         | 1X                                | 1X  | 1X                                    |            |
| Camera Mount:  | C-Mount                        |                         | C-Mount                           | F-Mount or C-Mount w/included adapter       | F-Mount or C-Mount w/included adapter |            |
| Objective Mount:   | M26 x 36 TPI                   |                         | M26 x 36 TPI                      | M26 x 36 TPI                                | M40 x 36 TPI                          |            |
| Max. Sensor Format:                                      | 2/3"                           |                         | 2/3"                              | APS-C                                       | APS-C                                 |            |
| Weight:  | 570g                           | 590g                    | 980g                              | 1400g                                       | 2150g                                 |            |
| Stock Number:  | <a href="#">#86-799</a>        | <a href="#">#89-621</a> | <a href="#">#89-622</a>           | <a href="#">#23-338</a>                     | <a href="#">#18-653</a>               |            |
| Manual Turret (Four Objective Mounts):                   | <a href="#">#86-589</a>        |                         | <a href="#">#86-589</a>           | <a href="#">#18-654</a>                     | <a href="#">#18-655</a>               |            |
| Compatible Objectives:                                   | MPlan Apo/HR/SL and G Plan Apo |                         | MPlan Apo/HR/SL and MPlan NIR/NUV | MPlan Apo/HR/SL G Plan Apo<br>MPlan Apo NIR | BD Plan Apo                           |            |
| VMU-L Laser Mount to C-Mount Adapter:                    | N/A                            |                         | <a href="#">#37-044</a>           | N/A   | N/A                                   |            |

