

TECHSPEC® UC Series Kit



UC Series: All lenses pictured may not be included in the kit. See "Contents of Kit" specification for included lenses.



Stock #25-608 **1 In Stock**

⊖ 1 ⊕ €1.260⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.260,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

UC Series **Product Family:**

Contents of Kit:
 8mm UC Series: [33-307](#)
 12mm UC Series: [33-303](#)
 16mm UC Series: [33-304](#)
 25mm UC Series: [33-305](#)
 35mm UC Series: [33-306](#)

Optical Properties

Working Distance (mm):

8mm UC Series: 50 - ∞
12mm UC Series: 100 - ∞
16mm UC Series: 200 - ∞
25mm UC Series: 200 - ∞
35mm UC Series: 200 - ∞

Aperture (f/#):

8mm UC Series: f/1.8 - f/11
12mm UC Series: f/1.8 - f/11
16mm UC Series: f/1.8 - f/11
25mm UC Series: f/1.85 - f/16
35mm UC Series: f/1.85 - f/16

Sensor

Maximum Sensor Format:

8mm UC Series: 1/2"
12mm UC Series: 1/1.8"
16mm UC Series: 1/1.8"
25mm UC Series: 1/1.8"
35mm UC Series: 1/1.8"

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Easy to Order Kits of Our Best Selling Fixed Focal Length Imaging Lenses
- Full Product Line or Select Focal Lengths Kit Versions Available
- TECHSPEC **C**, **UC**, and **HP** Imaging Lenses are Also Sold Individually

TECHSPEC® Imaging Lens Kits provide sets of TECHSPEC C, UC, and HP Imaging Lenses in easy to order kits at a reduced price. These kits offer multiple solutions to applications requiring fixed focal lengths such as factory automation, machine vision, inspection, or rapid prototyping. TECHSPEC Imaging Lens Kits can be ordered as a full product line or as curated selections of focal lengths within the product line. The TECHSPEC C, UC and HP lenses in these kits are C-Mount camera compatible, and feature a locking iris and focus adjustment to prevent unwanted adjustments.

- **C Series**: Compact (C), FALenses for Machine Vision
- **UC Series**: Ultra-Compact (UC), High Resolution Lenses for Small Sensors
- **HP Series**: High Performance (HP), C-Mount Lenses for Machine Vision