

LightPath 354260 | 6.5mm Dia., 0.16 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#37-099** 3-4 DAYS

[Other Coating Options](#)

-

1

+

€75,00

ADD TO CART

Qty 1-10
€75,00
Qty 11+
€66,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads
Diameter (mm): 6.50 ±0.015
Effective Focal Length EFL (mm): 15.29 @ 780nm
Numerical Aperture NA:

0.16
Substrate: D-ZK3
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 780
Coating: BBAR (600-1050nm)
Coating Specification: R _{abs} <1.0% @ 600 - 1050nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5
Edge Thickness ET (mm): 1.8
Center Thickness CT (mm): 2.21 ±0.05
f#: 3.12
Bevel: Protective bevel as needed
Compatible Window: Thickness: 0.25 (t) (mm) Material: BK7
Distance from Window to Lens (D) (mm): 12.727
Lightpath Lens Code: 354260
Operating Temperature (°C): ≤200
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 13.98
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant