

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 0.18X 1/2" Gold TL™ Telecentric Lens



#58-258 (0.18X)

Stock #58-258 3-4 DAYS



1



€2.260,00

ADD TO CART

Qty 1+

€2.260,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
196.30

Horizontal Field of View, 1/2" Sensor:
35.6mm

Filter Thread:
M72 x0.75 (Female)

Maximum Diameter (mm):
79.00

Weight (kg):

1.45
Numerical Aperture NA, Object Side: 0.015
Stock No. of Mounting Clamp: #56-026 Sold Separately
Resolution, Image Space MTF @ f/10: >60% @ 40 lp/mm
Number of Elements (Groups): 10 (7)
Note: GoldTL™
Typical Telecentricity @ 588nm (°): <0.040
Typical Distortion @ 588nm (%): 0.045
Type: Telecentric Lens
Primary Magnification PMAQ: 0.18X
Maximum Sensor Format: 1/2"
Working Distance (mm): 161 - 186
Mount: C-Mount
Aperture (f/#): f/6 - f/18
Coating: λ/4 MgF ₂
Depth of Field (mm): ±15.5 at f/10 (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 35.6 x 26.7
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View