

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 0.179X, 35mm M42 X 1.0 TitanTL® Telecentric Lens



TitanTL® Telecentric Lens

Stock #34-028 [CONTACT US](#)

1 **€11.075,00**

ADD TO CART

Qty 1+
€11.075,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Numerical Aperture NA, Object Side:
0.0056

Number of Elements (Groups):
7 (5)

Note:
TitanTL®

Type:
Telecentric Lens

Primary Magnification PMAG:

0.179X
Maximum Sensor Format: APS-H
Working Distance (mm): 351
Mount: M42 x 1.0
Aperture (f/#): f/16
Coating: λ/4 MgF ₂
Depth of Field (mm): ±26.6mm (20% @ 20 lp/mm, f/16)
Horizontal Field of View, APS-H Sensor: 163.1mm
FOV @ Max Sensor Format, H x V (mm): 163.1 x 112.8
Rear Filter Diameter (mm): 50.8
Typical Distortion @ 520nm (%): <0.2
Typical Telecentricity @ 520nm (°): <0.036
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View