

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region:

European Union

SUBMIT



0.19 - 20µm, 3W, Thermopile Wireless Power Detector

Stock #17-207 3-4 DAYS

-

1

+

€2.310,00

ADD TO CART

Qty 1+

€2.310,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
104 x 73 x 72

Weight (g):
367

Weight (kg):
0.367

Type of Sensor:
Thermopile

Active Area (mm):

12
Computer Interface: Bluetooth®
Maximum Incident Beam Power (mW): 3,000
Cooling Method: Convection
Maximum Incident Beam Power (W): 3
Maximum Incident Power Density (W/cm²): 1,000
Maximum Incident Power Density (kW/cm²): 1
Maximum Incident Energy Density (J/cm²): 1
Noise Level: 0.5 µW
Compatible Meters: Not Required
Wavelength Range (nm): 190 - 20000
Wavelength Range (µm): 0.19 - 20

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View