


# 0.2 OD 12.5mm Dia, Absorptive ND Filter

See More by [Hoya](#)



Stock #63-457  In Stock

⊖ 1 ⊕ **€31,00**

**ADD TO CART**

Qty 1-10

€31,00

Qty 11+

€28,00

Volume Pricing

[Request Quote](#)

**!** Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
12.50

**Optical Density OD (Average):**  
0.2 ±0.04

**Glass/Filter Number:**  
[Hoya ND50](#)

**Substrate:** □  
ND Filter Glass

**Coating:**  
Uncoated

**Index of Refraction  $n_d$ :**  
1.50

**Surface Quality:**  
80-50

**Transformation Temperature (°C):**  
495

**Thickness (mm):**  
1.50

**Thickness Tolerance (mm):**  
±0.5

**Transmission (%):**  
63.0 (average)

**Type:**  
Neutral Density Filter

**Blocking Wavelength Range (nm):**  
400 - 700

**Dimensional Tolerance (mm):**  
±0.1

**Parallelism (mm):**  
<0.02

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**REACH 201:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)