

LightPath 354062 | 6mm Dia., 0.24 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-706** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€65,00**

ADD TO CART

Qty 1-10
€65,00
Qty 11+
€57,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
6.00 ±0.015

Effective Focal Length EFL (mm):
11.00 @ 633nm

Numerical Aperture NA:
0.24

Substrate: D-ZK3
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (600-1050nm)
Coating Specification: R _{abs} <1.0% @ 600 - 1050nm
Surface Quality: 100-60
Clear Aperture CA (mm): 5.20
Edge Thickness ET (mm): 1.53
Center Thickness CT (mm): 2.25 ±0.05
f/#: 2.08
Bevel: Protective bevel as needed
Lightpath Lens Code: 354062
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Working Distance (mm): 9.700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant