

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



0.28X Magnification



Stock #62-921 3-4 DAYS



1



€5.455,00

ADD TO CART

Qty 1+

€5.455,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
197.50

Horizontal Field of View, 1/2" Sensor:
28.86mm

Horizontal Field of View, 2/3" Sensor:
39.69mm

Filter Thread:

M132 x0.75 (Female)
Maximum Diameter (mm): 138.6
Weight (g): 736
Horizontal Field of View, 1" Sensor: 57.73mm
Numerical Aperture NA, Object Side: 0.023
Stock No. of Mounting Clamp: #63-440 Sold Separately
Range Distance (mm): 17.5
Horizontal Field of View, 1.1" Sensor: 50.8mm
Number of Elements (Groups): 10 (7)
Note: CobaltTL
Horizontal Field of View, 1/1.8" Sensor: 32.47mm
Typical Telecentricity @ 588nm (°): <0.113
Typical Distortion @ 588nm (%): <0.008
Type: Telecentric Lens
Primary Magnification PMAG: 0.28X
Maximum Sensor Format: 1.1"
Working Distance (mm): 182
Mount: C-Mount
Aperture (f/#): f/6 - f/22
Coating: 425 - 675nm BBAR
Depth of Field (mm): ±12.44mm at f/10 (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 50.7 x 37.1
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View