

LightPath 354171 | 4.7mm Dia., 0.30 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-709** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€65,00**

ADD TO CART

Qty 1-10
€65,00
Qty 11+
€57,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
4.70 ±0.015

Effective Focal Length EFL (mm):
6.20 @ 633nm

Numerical Aperture NA:
0.30

Substrate: D-ZK3
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 80-50
Clear Aperture CA (mm): 3.70
Edge Thickness ET (mm): 2.88
Center Thickness CT (mm): 3.48 ±0.05
f/#: 1.67
Bevel: Protective bevel as needed
Lightpath Lens Code: 354171
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Working Distance (mm): 4.100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant