

0.35mm Dia, 670-1550nm, 0.0mm WD, Uncoated, GRIN Lens



Stock #88-355 3-4 DAYS

- 1 + **€82,00**

ADD TO CART

Qty 1-10
€82,00

Qty 11+
€72,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
0.35 +0.00/-0.01

Effective Focal Length EFL (mm):
0.30

Substrate: ☐
Aluminosilicate Glass Embedded with Silver Ions

f/#:

0.86
Numerical Aperture NA: 0.58
Coating: Uncoated
Type: Gradient Index Lens
Focal Length Specification Wavelength (nm): 670 - 1550
Gradient Constant (mm⁻¹): 2.02
Index of Refraction n_d - Center of Lens: 1.62
Length (mm): 0.78
Pitch: 0.25
Surface Quality: 40-20
Working Distance (mm): 0
Working Distance Tolerance (mm): ±0.01
Length Tolerance (%): ±5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
