

TECHSPEC® 0.367X CobaltTL Telecentric Lens



0.367X Magnification



Stock **#88-602** 3-4 DAYS

- 1 +

€2.180,00

ADD TO CART

Qty 1+

€2.180,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
163.50

Horizontal Field of View, 1/2" Sensor:
21.82mm

Horizontal Field of View, 2/3" Sensor:
30mm

Filter Thread:

M67 x 0.75 (Female)
Maximum Diameter (mm): 70.0
Weight (g): 627
Horizontal Field of View, 1" Sensor: 43.66mm
Numerical Aperture NA, Object Side: 0.031
Stock No. of Mounting Clamp: #89-721 Sold Separately
Range Distance (mm): 17.5
Horizontal Field of View, 1.1" Sensor: 38.41mm
Number of Elements (Groups): 10 (7)
Note: CobaltTL
Horizontal Field of View, 1/1.8" Sensor: 24.55mm
Typical Telecentricity @ 588nm (°): <0.114
Typical Distortion @ 588nm (%): <0.084
Type: Telecentric Lens
Primary Magnification PMAG: 0.367X
Maximum Sensor Format: 1.1"
Working Distance (mm): 169
Mount: C-Mount
Aperture (f/#): f/6 - f/16
Coating: 425 - 675nm BBAR
Depth of Field (mm): ±7.92mm at f/10 (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 38.4 x 28.8
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View