

0.420 - 1.08µm, 300mW, Silicon Power Detector



Photodetector with Attenuator

Stock **#89-309** 3-4 DAYS

- 1 + **€1.050,00**

ADD TO CART

Qty 1+
€1.050,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Filters Included :
OD 1.0 Attenuator

Dimensions (mm):
38.1 Dia. x27.4 T

Weight (g):
130

Weight (kg):
0.13

Type of Sensor:

Silicon
Active Area (mm): 10
Maximum Incident Beam Power (mW): 300
Maximum Incident Beam Power (W): 0.3
Maximum Incident Power Density (W/cm²): 100
Maximum Incident Power Density (kW/cm²): 0.1
Noise Level: 10 pW
Compatible Meters: Premier (#89-306) Deluxe (#89-305) USB (#89-307)
Wavelength Range (nm): 420 - 1080
Wavelength Range (µm): 0.420 - 1.08

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View