

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 0.5X, 110mm WD, In-Line Compact TL™ Telecentric Lens



110mm WD, 0.5X, In-Line Version (Left) and VS Version (Right)

Stock #67-303 3-4 DAYS



1



€1.065,00

ADD TO CART

Qty 1+

€1.065,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
170.00

Horizontal Field of View, 1/2" Sensor:
12.8mm

Horizontal Field of View, 2/3" Sensor:
17.6mm

Filter Thread:
M37 x0.75 (Female)

Maximum Diameter (mm):

40.00
Weight (g): 193
Horizontal Field of View, 1/3" Sensor: 9.6mm
Numerical Aperture NA, Object Side: 0.027
Working Distance Tolerance (mm): ±1
Number of Elements (Groups): 5 (5)
Note: CompactTL™
Typical Telecentricity @ 588nm (°): 0.064
Typical Distortion @ 588nm (%): 0.0202
Manufacturer: Edmund Optics®
Type: Telecentric Lens
Primary Magnification PMAG: 0.5X
Maximum Sensor Format: 2/3"
Working Distance (mm): 110
Mount: C-Mount
Style: In-Line Illumination
Aperture (f/#): f/9.3
Coating: N4 MgF ₂
Compatible Light Guide/Source: 1/4" (0.312") and 1/8" (0.187")
Depth of Field (mm): ±1.9mm (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 17.6 x 13.2
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View