

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



UV-NIR Neutral Density Filters

Stock #19-300 3-4 DAYS



1



€266,00

ADD TO CART

Qty 1-5

€266,00

Qty 6+

€238,70

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.2

Optical Density OD (Average):
0.6

Substrate: ☐

Fused Silica (Coming 7980)
Coating: Metallic Based ND
Surface Quality: 40-20
Thickness (mm): 5.00 ±0.10
Transmission (%): 25.0
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 190 - 1700
Clear Aperture (%): 80.00
Transmitted Wavefront, P-V: λ/4
Optical Density Tolerance (%): ±10
Parallelism (arcsec): <5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View