

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

LightPath 355390 | 4.5mm Dia., 0.55 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#83-616** 3-4 DAYS

[Other Coating Options](#)



1



€65,00

ADD TO CART

Qty 1-10

€65,00

Qty 11+

€57,50

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
4.50 ±0.015

Effective Focal Length EFL (mm):
2.75 @ 830nm

Numerical Aperture NA:

0.55
Substrate: D-ZLaF52LA
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 830
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 40-20
Clear Aperture CA (mm): 3.6
Edge Thickness ET (mm): 1.13
Center Thickness CT (mm): 1.90 ±0.04
f#: 0.91
Bevel: Protective bevel as needed
Lightpath Lens Code: 355390
Operating Temperature (°C): ≤200
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 2.16
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant