

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

0.59" X 0.59" , 0.12" Focal Length, Fresnel Lens



Aspherically Contoured Fresnel Lenses

Stock #13-455 [CONTACT US](#)

-

1

+

 €69,50

ADD TO CART

Qty 1-10

€69,50

Qty 11+

€60,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
3.00

Substrate: ☐
Acrylic

Coating:
Uncoated

Type: Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.08
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 0.59 x 0.59
Dimensions (mm): 15.0 x 15.0
Effective Focal Length EFL (inches): 0.12
Groove Density (grooves/inch): 250
Index of Refraction n _d : 1.49
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Transmission (%): 85 (Typical)

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View