

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

Norland Optical Adhesive NOA 86H, 1 oz. Application Bottle

See More by [Norland](#)



1 oz. Application Bottle of NOA

Stock #12-848 [CONTACT US](#)

- 1 +

 €87,00

ADD TO CART

Qty 1-4

€87,00

Qty 5+

€83,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Size (oz):
1

Glass Bonding:
Excellent

Metal Bonding:
Good

Plastic Bonding: Excellent/Good
Viscosity (cps): 250 - 350
Durability: Hard
Index of Refraction n_d: 1.55 @ 589nm
Norland Number: 86H
Shelf Life: 4 months
Type: Bottle
Typical Applications: Meets Bellcore specification of 85C/85RH for bonding glass. USP Class IV approved for medical applications. Cured with UV, visible light and/or heat.
Note: This adhesive should be refrigerated between 5 - 10°C when stored to maintain its optical properties.
Absorption Range (nm): 315 - 420
Bonding Type: Glass to Glass/Plastic
Energy for Full Cure (J/cm²): 2.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant