

TECHSPEC® 10 x 10mm Protected Gold Coated, λ/10 ZERODUR® Mirror



Stock **#39-861** 3-4 DAYS

⊖ 1 ⊕ **€109,00**

ADD TO CART

Qty 1-5
€109,00
Qty 6+
€87,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/10 (measured before coating)

Substrate: ☐
ZERODUR®

Back Surface:
Commercial Polish

Surface Quality: 20-10
Dimensions (mm): 10.0 x 10.0 +0.00/-0.20
Coating Specification: R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 2.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 700 - 10000
Length (mm): 10.00
Width (mm): 10.00
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.1
Damage Threshold, Reference:  0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant