

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



UV-NIR Neutral Density Filters

Stock #19-301 3-4 DAYS



1



€125,00

ADD TO CART

Qty 1-5

€125,00

Qty 6+

€112,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.2

Optical Density OD (Average):
0.9

Substrate: ☐

Fused Silica (Coming 7980)	
Coating:	Metallic Based ND
Surface Quality:	40-20
Thickness (mm):	1.50 ±0.10
Transmission (%):	12.5
Type:	Neutral Density Filter
Blocking Wavelength Range (nm):	190 - 1700
Clear Aperture (%):	80.00
Transmitted Wavefront, P-V:	λ/4
Optical Density Tolerance (%):	±10
Parallelism (arcsec):	<5
Regulatory Compliance	
RoHS:	Compliant
Certificate of Conformance:	View