

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

Norland Optical Adhesive NOA 1348, 1 oz. Application Bottle

See More by [Norland](#)



1 oz. Application Bottle of NOA (NOA60 shown as an example)



Stock #12-857 3-4 DAYS



1



€173,50

ADD TO CART

Qty 1-4

€173,50

Qty 5+

€164,90

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Size (oz):
1

Glass Bonding:
Good

Metal Bonding: Good
Plastic Bonding: Good
Viscosity (cps): 160
Durability: Soft Not Flexible
Index of Refraction n_d: 1.348 @ 589nm
Norland Number: 1348
Shelf Life: 4 months
Type: Bottle
Typical Applications: Low refractive index adhesive for bonding glass or plastic.
Absorption Range (nm): 315 - 450
Bonding Type: Glass to Glass
Energy for Full Cure (J/cm²): 6

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
