


TECHSPEC® 10 x 10mm, 0.33 Numerical Aperture, Uncoated, Square Precision Aspheric Lens



Stock #17-308 3-4 DAYS

- 1 + **€275,00**

ADD TO CART

Qty 1-5
€275,00
Qty 6+
€220,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
10.00 x 10.00

Effective Focal Length EFL (mm):
15.00 @ 587.6nm

Numerical Aperture NA:
0.33

Back Focal Length BFL (mm): 10.22
Substrate: N-SF6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 9.00 x 9.00
Edge Thickness ET (mm): 7.57
Center Thickness CT (mm): 8.62 ±0.10
f#: 1.50
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 390 - 2500
Conjugate Distance: Infinite
Power (diopters): 66.67

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View