

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #17-309 3-4 DAYS



1



€275,00

ADD TO CART

Qty 1-5

€275,00

Qty 6+

€220,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
10.00 x 15.00

Effective Focal Length EFL (mm):
11.25 @ 587.6nm

Numerical Aperture NA:
0.66

Back Focal Length BFL (mm): 5.71
Substrate:  N-SF6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <1
Surface Quality: 40-20
Clear Aperture CA (mm): 8.00 x 13.00
Edge Thickness ET (mm): 6.67
Center Thickness CT (mm): 10.02 ±0.10
f/#: 0.75
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 390 - 2500
Conjugate Distance: Infinite
Power (diopters): 88.89

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View