

TECHSPEC®

10.0mm Dia. x 10.0mm FL, VIS-NIR Coated, Plano-Convex Lens



Stock **#63-519** ☐ In Stock
[Other Coating Options](#)

-

1

+

€41,50

ADD TO CART

Qty 1-9
€41,50
Qty 10+
€37,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
10.00 +0.0/-0.025

Effective Focal Length EFL (mm):

10.00 @ 587.6nm
Back Focal Length BFL (mm): 8.18
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.25 ±0.05
Edge Thickness ET (mm): 1.45
Radius R₁ (mm): 7.85
Clear Aperture CA (mm): 9
f/#: 1.00
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View