

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

See More by [SCHOTT Optical Components](#)



Stock #17-263 [CONTACT US](#)



1



€40,00

ADD TO CART

Qty 1-5

€40,00

Qty 6+

€32,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm): 90 x 90
Dimensions (mm): 100.00 x 100.00
Thickness (mm): 1.10 Nominal
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 8.8 (+20 to +300°C)
Density (g/cm³): 2.48
Edges: Fine Ground
Index of Refraction n_d: 1.51
Knoop Hardness (kg/mm²): 639
Poisson's Ratio: 0.215
Substrate: SCHOTT Xensation®
Surface Quality: 80-50
Transformation Temperature (°C): 615
Type: Protective Window
Wavelength Range (nm): 380 - 840
Young's Modulus (GPa): 74
Length (mm): 100.00
Width (mm): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant