

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #15-185 CLEARANCE CONTACT US



1



€530,95

ADD TO CART

Qty 1+

€530,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
532

Focal Length FL (mm):
101.90

Maximum Diameter (mm):
83

Scan Angle (°):
±22.68

Scan Field (mm):
56.5 x 56.5

Mounting Threads: M85 x 1.0
Telecentricity (°): Not Specified
Transmission (%): ≥95
Type: F-Theta Lens
Working Distance (mm): 94.5
Wavelength Range (nm): 532
Range Distance (mm): 127.2
Focus Size Diameter, 1/e² (μm): 8.5
Input Beam Diameter, 1/e² (mm): 12
Maximum Length (mm): 64.5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View