


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 1030nm, 12.7mm Dia., 45° Thin Film Polarizer



TECHSPEC® Ultrafast Thin Film Polarizers

Stock #13-055 3-4 DAYS



1



€334,00

ADD TO CART

Qty 1-4

€334,00

Qty 5+

€295,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
45 ±1

Coating:
Thin Film Dielectric

Design Wavelength DWL (nm):
1030

Diameter (mm): 12.70 +0.00/-0.10
Extinction Ratio: 1000:1
Substrate: □ Fused Silica (Corning 7980)
Surface Quality: 10-5
Thickness (mm): 3.00 ±0.10
Type: Linear Polarizer
Parallelism (arcmin): <3
Clear Aperture (%): 85
Transmitted Wavefront, P-V: λ/10 @ 633nm
Coating Specification: S1: R _s >99.8% @ 1030nm, T _p >98% @ 1030nm S2: R _p <0.1% @ 1030nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View