

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 101.6 X 152.4mm EFL 90° Protected Silver 100A Off-Axis Parabolic Mirror



Stock #36-602 3-4 DAYS

[Other Coating Options](#)



1



€1.005,00

ADD TO CART

Qty 1-5

€1.005,00

Qty 6+

€904,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
101.60 +0.00/-0.38

Effective Focal Length EFL (mm):

152.40
Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 152.40
Coating: Protected Silver (450-12000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥98% @ 2,000 - 12,000nm, R _{avg} (typical) 96% @ 450 - 2,000nm
Off-Set Angle (°): 90
Parent Focal Length PFL (mm): 76.2
Surface Figure, RMS: 1λ
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 450 - 12000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #83-977
Substrate: Aluminum 6061-T6
Y Offset (mm): 152.4
Reflected Wavefront, RMS: 2λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant