

1070nm, 8-12mm Dia. Input Beam, HP Sapphire Focal Flat Top Beam Shaper | Focal πShaper_1070_Q-10_HP

See More by [AdlOptica](#)



Stock #17-593 3-4 DAYS

⊖ 1 ⊕ **€4.090,00**

ADD TO CART

Qty 1-4
€4.090,00

Qty 5+
€3.682,00

Volume Pricing
[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
10

Design Wavelength DWL (nm):
1070

Diameter (mm):
42.00

Model Number:
πShaper_1070_Q-10_HP

Length (mm):
29.00

Transmission (%):
>99

Type:
Beam Shaper (Sapphire)

Weight (g):
50

Wavelength Range (nm):
1020 - 1100

Input Beam Diameter, 1/e² (mm):
8 - 12

Maximum Input Power, CW (kW):
3

Inner Thread:
M30 x 0.75

Outer Thread:
M30 x 0.75

Compatible Adapter:
[#12-322](#)

Input Beam Mode:
TEM₀₀

Typical Input Beam Mode Quality, M²:
<1.5

Input Beam Divergence (mrad):
±20

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Compliant](#)
