

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #16-768 [CONTACT US](#)



1



€3.180,00

ADD TO CART

Qty 1+

€3.180,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Focal Length FL (mm):
103.00

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Model Number:
017700-402-26

Maximum Diameter (mm):
99.8 +0/-0.1

Scan Angle (°):

±20.1
Scan Field (mm): 50 x 50
Mounting Threads: M85 x 1
Telecentricity (°): F-Theta Only: 2.40 With Scanner: 2.80
Type: JENar Silverline F-Theta
Weight (g): 700
Working Distance (mm): 134.85
Note: Damage Warning: Not recommended for picosecond and femtosecond laser pulses.
Wavelength Range (nm): 355
Protective Window: #17-690 : One Included
Manufacturer: Jenoptik
Damage Threshold, By Design: ☐ $1.0 \text{ J/cm}^2 * (\tau/\text{[ns]})^{0.40}$ 1.0 MW/cm ²
Scan Field Diameter (mm): 71
X/Y Mirror Angle (°): ±7.2
Flange Distance (mm): 176.95
Focus Size Diameter, 1/e² (µm): 8
GDD Specification (fs²): 5670
Input Beam Diameter, 1/e² (mm): 9
Maximum Length (mm): 66.5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View