

TECHSPEC® 10X, 532nm Vega® Nd:YAG Laser Line Beam Expander



10X, 532nm DABeam Expander, #35-116

Stock **#35-116** 3-4 DAYS

⊖ 1 ⊕

€483,00

ADD TO CART

Qty 1-9

€483,00

Qty 10+

€426,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Coating:
Laser V-Coat (532nm)

Design Wavelength DWL (nm):
532

Entrance Aperture (mm): 7.5
Exit Aperture (mm): 26
Expansion Power: 10X
Substrate: ☐ Fused Silica (Corning 7980)
Length (mm): 83.10
Mounting Threads: Input: Male M30 x 1 Output: Female M34 x 0.5 (not intended for use)
Transmission (%): >98.5 (nominal)
Type: Beam Expander
Weight (g): 175
Housing Diameter (mm): 39.95
Transmitted Wavefront, P-V: <λ/10 for 2.3mm input beam (nominal, λ = DWL)
Coating Specification: R _{abs} <0.25% @ 532nm
Wavelength Range (nm): 500 - 570
Style: Fixed Magnification
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns, 20Hz
Divergence Adjustment: Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View