


10600nm, 8-12mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal πShaper_CO2_Q-10

See More by [AdlOptica](#)



Stock #17-592 3-4 DAYS

- 1 + **€4.468,00**

ADD TO CART

Qty 1-4
€4.468,00

Qty 5+
€4.019,00

Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
20

Design Wavelength DWL (nm): 10600
Diameter (mm): 42.00
Model Number: πShaper_CO2_Q-10
Length (mm): 29.00
Transmission (%): >99
Type: Beam Shaper (ZnSe)
Weight (g): 50
Wavelength Range (nm): 9000 - 11000
Input Beam Diameter, 1/e² (mm): 8 - 12
Maximum Input Power, CW (kW): 0.2
Inner Thread: M30 x 0.75
Outer Thread: M30 x 0.75
Compatible Adapter: #12-322
Input Beam Mode: TEM ₀₀
Typical Input Beam Mode Quality, M²: <1.5
Input Beam Divergence (mrad): ±20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant