

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 1064nm, 45°, 6.35mm Dia., 4mm Thick, Nd:YAG IBS Laser Line Mirror



Stock #12-525 3-4 DAYS

1 €140,00

ADD TO CART

Qty 1-5

€140,00

Qty 6+

€123,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%): 85
Back Surface: Commercial Polish
Coating Specification: R_{abs} >99.95% @ 1064nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror, IBS (1064nm)
Design Wavelength DWL (nm): 1064
Diameter (mm): 6.35 +0.00/-0.10
Thickness (mm): 4.00 ±0.20
Angle of Incidence (°): 45
Substrate: Fused Silica (Corning 7980)
Damage Threshold, Certified: 15 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View