

10mW, 850nm Alignment Laser Diode



Red and IR Alignment Laser Diode

Stock **#37-040** 3-4 DAYS

⊖ 1 ⊕ **€161,00**

ADD TO CART

Qty 1-9
€161,00
Qty 10+
€142,20
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
-10 to 50

Operating Voltage (V):
5

Output Power (mW): 10
Wavelength (nm): 850.00
Wavelength Tolerance (nm): ±5
Power Supply: Power Supply Required and Sold Separately: USA: #83-855 Europe: #83-855 Japan: #13-640 Korea: #33-770 China: #83-855
Modulation Frequency (kHz): 0 - 10
Beam Diameter (mm): 3 x 1 Typical
Beam Divergence (mrad): Major Axis: 0.5 Minor Axis: 0.2
Laser Class - CDRH: IIIb
Color: Infrared
Length (mm): 36.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant