

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 10mm Dia., 0.63 NA, Uncoated, NIR Aspheric Lens



TECHSPEC® Near-Infrared (NIR) Aspheric Lenses

Stock #13-496 3-4 DAYS

[Other Coating Options](#)



1



€165,00

ADD TO CART

Qty 1-5

€165,00

Qty 6+

€132,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
10.00 +0.00/-0.10

Effective Focal Length EFL (mm):
8.00 @780nm

Numerical Aperture NA:

0.63
Back Focal Length BFL (mm): 5.92
Substrate: □ S-LAH64
Aspheric Design Wavelength (nm): 780
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 9
Edge Thickness ET (mm): 1.57
Center Thickness CT (mm): 3.70 ±0.10
f#: 0.80
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 375 - 2100
Conjugate Distance: Infinite
Power (diopters): 125.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View