

TECHSPEC® 10° Nom. 12.5mm Dia. Uncoated, N-BK7 Wedge Prism



Stock **#35-740** 3-4 DAYS

- 1 + **€37,50**

ADD TO CART

Qty 1-5
€37,50

Qty 6+
€30,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Uncoated

Angle Tolerance (arcsec):
±30

Bevel:
Protective bevel as needed

Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1
Design Wavelength DWL (nm): 632.8
Diameter (mm): 12.50 +0.00/-0.10
Edge Thickness ET (mm): 1.5
Image Orientation: Beam Deviation
Power (diopters): 17.63
Ray Deviation @ 633nm (°): 10.00
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 1.50
Type: Wedge Prism
Wavelength Range (nm): 350 - 2200
Wedge Angle: 18° 8'

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View