


10mm Dia., 0.7mm Thick, Coherent® Uncoated Polycrystalline CVD Diamond Window

See More by [Coherent®](#)



Stock #12-669 3-4 DAYS

- 1 + **€1.975,00**

ADD TO CART

Qty 1-10

€1.975,00

Qty 11+

€1.777,50

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture (%):
≥90

Clear Aperture CA (mm):
9.00

Diameter (mm): 10.00 ±0.05
Thickness (mm): 0.70 ±0.10
Coating: Uncoated
Index of Refraction n_d: 2.38 @ 10.6μm
Parallelism (arcmin): <5
Substrate: Coherent® Optical Grade Polycrystalline CVD Diamond
Surface Quality: 40-20
Type: Protective Window
Wavelength Range (nm): 300 - 25000

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View