

## 10mm Aperture VIS/NIR Fiber Optic Collimator, SMA



Fiber Optic Collimator, SMA (SMA adapter inserted)



Stock #88-180  In Stock

1 **€220,00**

**ADD TO CART**

Qty 1-10

€220,00

Qty 11+

€194,00

Volume Pricing

[Request Quote](#)

**!** Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Diameter (mm):**  
15.88

**Substrate:**   
[N-BK7](#)

**Type:**  
Fiber Collimator

**Wavelength Range (nm):**  
350 - 2200

**Aperture Size:**  
10.0

**Compatible Fiber NA:**  
0.22

**Connector:**  
SMA

**Fiber Diameter (µm):**  
compatible 400 to 800

**Focal Length FL (mm):**  
18.00

**Housing Material:**  
Anodized Aluminum

**Length (mm):**  
34.29

**Note:**  
Compatible with [#88-182](#), [#88-183](#), [#88-184](#), [#88-185](#), [#88-186](#), & [#88-187](#) Refocusing Assemblies

**Operating Temperature (°C):**  
-40 to 100

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Reach 209:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

---