

TECHSPEC® 10mm Dia x 15mm EFL Hastings Triplet Achromatic Lens



Stock **#67-418** 3-4 DAYS

⊖ 1 ⊕ **€110,00**

ADD TO CART

Qty 1-5
€110,00

Qty 6+
€88,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
10.00 +0.0/-0.025

Effective Focal Length EFL (mm):
15.00

Focal Length Tolerance (%):
±2

Back Focal Length BFL (mm): 11.21
Focal Length Specification Wavelength (nm): 587.6
Centering (arcmin): <3
Center Thickness CT (mm): 10.00
Center Thickness A (mm): 8.00
Center Thickness B (mm): 1.00
Radius R ₁ (mm): 11.33
Radius R ₂ (mm): 6.17
Radius R ₃ (mm): -6.17
Radius R ₄ (mm): -11.33
Edge Thickness ET (mm): 7.67
Substrate:  N-F2 / N-BK7 / N-F2
Surface Quality: 40-20
f/#: 1.5
Numerical Aperture NA: 0.33
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Triplet Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View