

TECHSPEC® 10mm λ /20, 355nm V-Coat, Nd:YAG Right Angle Prism



TECHSPEC Nd:YAG Laser Line λ /20 UV Fused Silica Right Angle Prisms

Stock **#37-623** 3-4 DAYS



1



€312,00

ADD TO CART

Qty 1-5

€312,00

Qty 6+

€249,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle Tolerance (arcsec):
±15

Coating:
Laser V-Coat (355nm)

Design Wavelength DWL (nm):
355

Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 20-10
Type: Right Angle Prism
Dimensional Tolerance (mm): +0.00/-0.10
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Length of Hypotenuse (mm): 14.10
Length of Legs (mm): 10.00
Pyramid Tolerance (arcmin): ±1
Image Orientation: Left-Handed
Coating Specification: R_{abs} <0.25% @ 355nm
Surface Flatness (P-V): λ/20
Damage Threshold, By Design: ☐ 7.5 J/cm², 20ns, 20 Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View