

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

10mW, 405nm Violet Alignment Laser Diode Module



Violet Alignment Laser Diode

Stock #37-025 3-4 DAYS



1



€385,00

ADD TO CART

Qty 1-9

€385,00

Qty 10+

€347,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
15 to 30

Operating Voltage (V):
5

Output Power (mW): 10
Wavelength (nm): 405.00
Wavelength Tolerance (nm): ±5
Power Supply: Power Supply Required and Sold Separately. USA: #83-855 Europe: #83-855 Japan: #13-640 Korea: #33-770 China: #83-855
Modulation Frequency (kHz): 0 - 10
Beam Diameter (mm): 3.5 Typical
Beam Divergence (mrad): <0.5
Laser Class - CDRH: IIIb
Color: Violet
Length (mm): 36.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
