

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.7mm Dia. 515nm 45°, Yb:YAG Laser Line Mirror



TECHSPEC® Yb:YAG Laser Line Mirrors

Stock #38-872 3-4 DAYS



1



€132,00

ADD TO CART

Qty 1-5

€132,00

Qty 6+

€119,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality:  
10-5

Type:  
Laser Mirror

Parallelism (arcmin):  
<3

|                                                                                                                     |
|---------------------------------------------------------------------------------------------------------------------|
| <div>Clear Aperture (%):<br/>90</div>                                                                               |
| <div>Back Surface:<br/>Commercial Polish</div>                                                                      |
| <div>Reflection at DWL (%):<br/>99.8</div>                                                                          |
| <div>Coating Specification:<br/>R<sub>abs</sub> &gt;99.8% @ 515nm<br/>R<sub>avg</sub> &gt;99.5% @ 509 - 520nm</div> |
| <div>Wavelength Range (nm):<br/>509 - 520</div>                                                                     |
| <div>Surface Flatness (P-V):<br/>λ/10</div>                                                                         |
| <div>Coating Type:<br/>Dielectric</div>                                                                             |
| <div>Coating:<br/>Laser Mirror (509-520nm)</div>                                                                    |
| <div>Design Wavelength DWL (nm):<br/>515</div>                                                                      |
| <div>Diameter (mm):<br/>12.70 +0.00/-0.10</div>                                                                     |
| <div>Thickness (mm):<br/>6.35 ±0.2</div>                                                                            |
| <div>Angle of Incidence (°):<br/>45</div>                                                                           |
| <div>Substrate: <input type="checkbox"/><br/><a href="#">Fused Silica</a> (Corning 7980)</div>                      |
| <div>Damage Threshold, By Design: <input type="checkbox"/><br/>15 J/cm² @ 515nm, 20ns, 20Hz</div>                   |

### Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS:<br/><a href="#">Compliant</a></div>                  |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |